


Kernstifte

MOLDMAX HH (Radius Stift/Kopf max.: 0,8 mm):

Stiftdurchmesser	4 mm	6 mm	8 mm	10 mm
Kopfdurchmesser	8 mm	12 mm	14 mm	16 mm
Kopfhöhe	3 mm	5 mm	5 mm	5 mm
Länge	300 mm	300 mm	300 mm	300 mm
Toleranzen	+0/-0,025 mm	+0/-0,4 mm	+0/-0,05 mm	±0,25 mm



QRO® 90 HT: Stiftdurchmesser 6-45 mm, vergütet auf 37-41 HRC, Entkohlung max. 0,6 mm

Durchmesser	6,0	8,0	10,0	12,7	16,0	18,0	20,0
Toleranzen	+0,1/+0,2	+0,2/+0,2	+0,2/+0,2	+0,3/+0,7	+0,2/+0,2	+0,1/+0,2	+0,1/+0,2
Max. Fertigmaß	5,0	7,0	9,0	12,0	15,0	17,0	19,0

Durchmesser	22,0	25,4	28,0	30,0	35,0	41,0
Toleranzen	+0,1/+0,2	+0,1/+0,2	+0,1/+0,2	+0,1/+0,2	+0,1/+0,2	+0,1/+0,2
Max. Fertigmaß	21,0	24,5	27,0	29,0	34,0	40,0